

# PRODUCT SHEET

07/09/20





## **MONO-ROLL** - manual non-woven disposable cloth



Date of issue:

| REF.        | NOTES                     | NET WEIGHT<br>(kg) | PCK | VOLUME<br>(m³) | GROSS WEIGHT<br>(kg) | SIZE (cm) |
|-------------|---------------------------|--------------------|-----|----------------|----------------------|-----------|
| 00PU0203000 | Pack: 6 rolls of 90 tears | 2,4                | 1   | 0,025          | 2,83                 | 32x28     |

### **APPLICATIONS**

Cloth suitable for manual surface washing. A double tear combined to Spillo holder can be used for cleaning large and more difficult to reach surfaces. In industry it is recommended for its high oil absorption capacity and good resistance to solvents.. Suitable to be used with disinfectants.

#### **FEATURES**

- The non-woven fibres with special pierced layer grant an effective dirt collection and reduce the accidental tearing risk compared to paper
- The cloth has an excellent absorbance capacity and provides a homogeneous solution release
- · Central single cloth pull out
- The roll can be used with 4 L bucket with hermetic cover. The cloths are soaked with cleaning/disinfecting solution directly into the bucket and then used individually by pulling them out of the central opening of the cover
- Each tear has a surface covering of 10/12 m²
- Roll size: 20x13,5x14 cm

#### **MATERIAL**

65% viscose and 35% polyester Weight: 50 g/m<sup>2</sup>

## **ABSORBENCY**

Single cloth absorbs 16-20 ml We recommend the use of 1.5 -1.8 lt of solution per roll

## RELATED PRODUCTS



4 It plastic bucket with handle and hermetic cover with central slot for cloth extraction



Graduated plastic jar



Plastic holder for hand duster SPILLO